

ENGLISH

Datasheet

RS Pro HSS M10 89 mm Counterbore Drill Bit, 18mm Cutter Diameter, 10 mm Screwed Shank

RS Stock No: 522-7474



Product Details

RS Pro counterbore drill bit has HSS construction with M10 thread size. This 89 mm long drill bit has a cutter diameter of 18 mm and screwed shank diameter of 10 mm. The right hand cutting counterbore is designed to produce recessed holes for cap headed screws.

Features and Benefits

- 19 mm cutter length
- 11 mm pilot length
- Pilot diameter of 10.5 mm
- Threaded shank
- 89 mm overall length
- Made from HSS



ENGLISH

Specifications:

Cutter Diameter	18 mm
Cutter Length	19 mm
Material	HSS
Overall Length	89 mm
Pilot Diameter	10.5 mm
Pilot Length	11 mm
Shank Diameter	10 mm
Shank Type	Screwed
Thread Size	M10
Number of Flutes	2