


# Data sheet

## SMA PLUG CRIMP ST.+SMA PLUG CRIMP ST.+RG-316U

RS stock No: **5260487**

NO	DESCRIPTION	DATE
△	ADD 19 REF. BACKGROUND FORMAT UPDATED	03.07.11'
△	1.5 MAX. (L=250 MM)	07.04.12'



**1.0 ELECTRICAL**

- 1.1 FREQUENCY RANGE: DC-3 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 WORKING VOLTAGE: 335 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 750 VOLTS
- 1.5 VSWR: 1.5 MAX. (L=250 MM) △

**2.0 MATERIALS**

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1487 AND ASTM D1710
- 2.4 CRIMP FERRULE: BRASS PER JIS-C2700

**3.0 FINISHES AND OTHERS**

3.1 SEE BELOW TABLE FOR DETAILS.

**4.0 MECHANICAL**

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 CABLE RETENTION 15 lbs MIN.

**5.0 ENVIRONMENTAL**

5.1 OPERATING TEMPERATURE RANGE: -55° C TO +105° C

NO	DESCRIPTION	Q'TY	FINISH
3	HEAT SHRINK TUBE	2	BLACK
2	CABLE	1	RG-316U
1	19-03-3 174U(500)	2	T.G.G

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		SMA PLUG CRIMP ST.+SMA PLUG CRIMP ST.+RG-316U	
製圖	DRAWN <i>Yoko</i>	TOLERANCE X ±0.2	品名 YH46-26
檢圖	CHECK <i>Arc</i>	XX ±0.1	TITLE ROHS COMPLIANT
認定	APPROVAL <i>Angela</i>	XXX ±0.05	DATE 12.03.03'
		ANGLE ±5°	版次 A-2
		UNIT mm(in)	DWG.NO. 99-0315
		SCALE 4:1	

