

Professionally approved products.

Datasheet ST Adaptors

RS Stock number [536-7752](#)



Description:

Our ST adaptors have high precision alignment sleeves for reliability and better reconnectability. ST adaptors come with a ceramic sleeve for the singlemode adaptor and phosphor bronze sleeve for the multimode adaptor. The simplex housing is available in double D footprint type.

Specifications:

	Ceramic	Phosphor Bronze	Conformance
Insertion Loss (typ)	0.1dB	0.15dB	IEC 61300-3-4
Mating Durability	500	500	IEC 61300-2-2
Receptacle Retention Force	2N-5.9N	2N-5.9N	IEC 61754-2
Operating temperature	-25 to +70, 12 cycles	-25 to +70, 12 cycles	IEC 61300-2-22

Professionally approved products. Datasheet

Features:

- Complies with IEC 61754-2
- Low insertion loss and high reconnectability
- REACH SvHC compliant
- Materials compliant to RoHS2
- Available in simplex or duplex

Applications:

- Data processing networks
- Premises distribution