



Cable and Fibre Type

Grade of the cable: LSZH

Fibre type (ISO/IEC 11801-2002)		Outer Sheath Colour
62.5/125	OM1	Orange
50/125	OM2	Orange
50/125	OM3	Purple
09/125	OS1	Yellow

Optical Performance (IEC 61300-3-4):

Multimode (@ 1300nm)
 Max. IL - 0.30dB Typical: 0.20dB
Singlemode: (@ 1310nm and/or 1550nm)
 Max. IL - 0.30dB Typical: 0.20dB Return Loss: >50dB

RoHS Compliant

Coiling Diameter: Coiling Diameter of the patchcord shall be greater than 200mm

Packing: Each product shall be individually bagged and identified with a unique number printed on an ID label affixed to the product. Also, each product will be supplied with a Test Certificate.

Id No.	Description	Ea
1.	SC Connector	1
2.	SC Boot	1
3.	ST Connector	1
4.	ST Boot	1
5.	Identification Label	1
6.	2.8mm Simplex Cable (L m)	1

REV	DESCRIPTION	DATE	BY	CHKD	DATE	BY	CHKD

FINISH	SCALE	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PART NO.	QTY	REV	QTY	REV
-	Not to Scale	0 PLC ± 0.04 1 PLC ± 0.04 2 PLC ± 0.04 3 PLC ± 0.04 4 PLC ± 0.04	SC-ST Simplex PATCHCORD		01		

ALL DIMENSIONS IN MM	ANGLES	2 ANG	
----------------------	--------	-------	--

--	--	--	--	--	--	--	--	--	--