


Data Sheet

D-SUB WITH 9-PIN MALE CONNECTOR BY MACHINING

RS stock No: 5443733




NO	DESCRIPTION	DATE
△	ADD MIS PART NO.	04.01.04
△	ADD DESCRIPTION 24.99±0.13 → 24.99±0.25 16.92±0.13 → 16.92±0.25 #3.05 → #3.05±0.25 8.36 → 8.36±0.25 12.55 REF. → 12.55±0.38 2.77 → 2.77±0.38 19.28 REF. → 19.28±0.38 1 → 0.76±0.25 (5.97) → 5.95±0.38 10.72 REF. → 10.72±0.38 11 REF. → 10.72±0.38 3.3 REF. → 2.74±0.5 2.84 → 2.84±0.38 TIN → GOLD MIS PART NO. → P/N	10.02.07
△	GOLD	03.16.13



CONTACT TYPE
 COLOR OF INSULATION
 PLATING OF CONTACT
 SOLDER TERMINATIONS
 WORKING VOLTAGE
 CONTACT RESISTANCE
 MATING CYCLES
 PLUG

MACHINED CONTACT
 BLACK PBT GLASSFIBRE REINFORCED
 △ GOLD
 △ GOLD
 △ GOLD
 500V AC AT SEA LEVEL
 10m OHM MAX.
 150 TIMES
 DIMPLED



△△ P/N: 544-3733

APPROVED by _____ DATE: _____

DESCRIPTION		D-SUB WITH 9-PIN MALE CONNECTOR BY MACHINING						
製圖	DRAWN	TOLERANCE	品名	050-0009P-M	日期	DATE	版次	REV.
	Yoko	.X ±0.2	TITLE	\R0HS COMPLIANT	日期	01.09.08	次	A-3
檢圖	CHECK	.XX ±0.1	單位	DWG.NO.	55-0043			
	Ivan	.XXX ±0.05	mm(in)					
認定	APPROVAL	.XXX ±0.05	比例	SCALE				
	Angela	ANGLE ±5°	比例	2:1				

