

Data sheet

D-SUB WITH 9-PIN FEMALE CONNECTOR BY FORMING

RS stock No: 5443749

NO	DESCRIPTION	DATE
▲	ADD M/S PART NO.	04.01.04
▲	ADD DESCRIPTION ADD 6.2±0.38	
	24.99±0.13 — 24.99±0.25	
	16.33±0.13 — 16.33±0.25	
	9.05 — 9.05±0.25	
	7.9 — 7.9±0.25	
▲	12.55 REF. — 12.55±0.38	03.13.08
	2.77 — 2.77±0.38	
	19.28 REF. — 19.28±0.38	
	1 — 0.76±0.25	
	10.72 REF. — 10.72±0.38	
	11 REF. — 10.72±0.38	
	3.3 REF. — 2.8±0.7	
	2.84 — 2.84±0.38	
	M/S PART NO. — P/N	
▲	CORRECT DIMENSION LINE POSITION	12.02.11

CONTACT TYPE FORMED CONTACT
 COLOR OF INSULATION WHITE PBT GLASSFIBRE REINFORCED
 PLATING OF CONTACT GOLD <5 MICRO INCHES>
 SOLDER TERMINATIONS TIN
 WORKING VOLTAGE 500V AC AT SEA LEVEL
 CONTACT RESISTANCE 10m OHM MAX.
 MATING CYCLES 150 TIMES

▲▲ P/N: 544-3749

APPROVED by _____ DATE: _____

DESCRIPTION		D-SUB WITH 9-PIN FEMALE CONNECTOR BY FORMING	
製 圖	DRAWN <i>Gina</i>	TOLERANCE .X ±0.2	品名 050-0009S-F
檢 查	CHECK <i>Jase</i>	UNIT mm(in)	DATE 02.22.95
審 定	APPROVAL <i>Angela</i>	SCALE 2:1	REV. A-3
			TITLE ROHS COMPLIANT
			DWG. NO. 55-0044

