

Data Sheet

D-SUB WITH 15-PIN MALE CONNECTOR BY MACHINING



RS stock No: 5443777

NO	DESCRIPTION	DATE
▲	ADD MIS PART NO.	04.01.04
▲	ADD DESCRIPTION 33.32±0.13 → 33.33±0.25 25.25±0.13 → 25.25±0.25 ø3.05 → ø3.05±0.25 ø3.36 → ø3.36±0.25 12.55 REF. → 12.55±0.38 2.77 → 2.77±0.38 27.51 REF. → 27.51±0.38 1 → 0.76±0.25 (5.97) → 5.95±0.38 10.72 REF. → 10.72±0.38 11 REF. → 10.72±0.38 3.3 REF. → 2.7±0.5 2.84 → 2.84±0.38 TIN → GOLD MIS PART NO. → P/N	03.13.08
▲	GOLD	05.16.13

CONTACT TYPE: MACHINED CONTACT
 COLOR OF INSULATION: BLACK PBT GLASSFIBRE REINFORCED
 PLATING OF CONTACT: GOLD
 SOLDER TERMINATIONS: GOLD
 WORKING VOLTAGE: 500V AC AT SEA LEVEL
 CONTACT RESISTANCE: 10m OHM MAX.
 MATING CYCLES: 150 TIMES
 PLUG: DIMPLED

▲▲ P/N: 544-3777

APPROVED by _____ DATE: _____

製圖	DRAWN	TOLERANCE	品名	050-0015P-M	日期	DATE	版次	REV.
Yoko	X	±0.2	TITLE	ROHS COMPLIANT	02.23.95		A-3	
檢圖	CHECK	.XX ±0.1	單位	mm(in)	DWG.NO. 55-0047			
Ivan	.XXX	±0.05	SCALE					
認定	APPROVAL	ANGLE ±5°	比例	2:1				
Angela								

