

Data sheet

D-SUB WITH 37-PIN FEMALE CONNECTOR BY FORMING

RS stock No: 5443878

NO	DESCRIPTION	DATE
▲	ADD MJS PART NO.	04.01.04
▲	ADD DESCRIPTION ADD 6.240.38	
▲	65.93±0.38 — 65.35±0.38	03.03.08
▲	64.18±0.43 — 63.84±0.25	
▲	52.42±0.13 — 54.02±0.25	
▲	#3.05 — #3.05±0.25	
▲	7.9 — 7.9±0.25	
▲	12.55 REF. — 12.55±0.38	
▲	2.77 — 2.77±0.38	
▲	53.32 REF. — 57.74±0.38	
▲	1 — 0.76±0.25	
▲	10.72 REF. — 10.72±0.38	
▲	11 REF. — 10.72±0.38	
▲	3.3 REF. — 2.81.7	
▲	2.84 — 2.84±0.38	
▲	MJS PART NO. — P/N	
▲	CORRECT DIMENSION LINE POSITION	12.02.11

CONTACT TYPE: FORMED CONTACT
 COLOR OF INSULATION: WHITE PBT
 PLATING OF CONTACT: GLASSFIBRE REINFORCED GOLD (<5 MICRO INCHES>)
 SOLDER TERMINATIONS: TIN
 WORKING VOLTAGE: 500V AC AT SEA LEVEL
 CONTACT RESISTANCE: 10m OHM MAX.
 MATING CYCLES: 150 TIMES

▲▲ P/N: 544-3878

APPROVED by _____ DATE: _____

DESCRIPTION		D-SUB WITH 37-PIN FEMALE CONNECTOR BY FORMING	
製圖	DRAWN	TOLERANCE	公差
Cina		X ±0.2	050-0037S-F
檢圖	CHECK	.XX ±0.1	ROHS COMPLIANT
Jase		.XXX ±0.05	DWG.NO. 55-0056
認定	APPROVAL	ANGLE ±5°	比例 2:1
Angela			

