



Data Sheet

D-SUB WITH 37-PIN FEMALE CONNECTOR BY MACHINING

RS stock No: 5443884



NO	DESCRIPTION	DATE
⚠	ADD MIS PART NO.	04.01.04
⚠	ADD DESCRIPTION ADD 6.2±0.38 66.93±0.38 → 69.35±0.38 61.12±0.13 → 63.5±0.25 52.42±0.13 → 54.83±0.25 ø3.05 → ø3.05±0.25 7.9 → 7.9±0.25 12.55 REF. → 12.55±0.38 2.77 → 2.77±0.38 55.32 REF. → 57.7±0.38 1 → 0.76±0.25 10.72 REF. → 10.72±0.38 11 REF. → 10.85±0.38 3.3 REF. → 2.4±0.5 2.84 → 2.84±0.38 TIN → GOLD MIS PART NO. → P/N	03.14.08
⚠	CORRECT DIMENSION LINE POSITION	12.02.11
⚠	CORRECT DIMENSION LINE POSITION	03.05.12
⚠	GOLD	05.16.13



⚠ ⚠ P/N: 544-3884

APPROVED by _____ DATE: _____

DESCRIPTION		D-SUB WITH 37-PIN FEMALE CONNECTOR BY MACHINING						
製圖	DRAWN	TOLERANCE	品名	□50-0037S-M	日期	DATE	版次	REV.
檢圖	Yoko	X	±0.2	TITLE	NRDHS COMPLIANT	02.23.95	A-5	
檢圖	CHECK	XX	±0.1	單位	UNIT			
認定	Iwan	.XXX	±0.05	mm(in)	DWG.NO.	55-0057		
認定	APPROVAL	ANGLE	±5°	比例	SCALE			
	Angela				2:1			