

Professionally approved products.

Datasheet

Hydraulic Crimp Tool, 25-185 sq.mm

RS Stock number [624-1285](#)



Description:

This robust hydraulic crimping tool is compact and ideal for working in confined spaces. Having the benefit of spring loaded handles, the dies can be advanced using only one hand, therefore leaving the other hand free to position the connector.

- Supplied with 6 die sets: 10mm², 35mm², 70mm², 95mm², 150mm² and 185mm² (Replacement die sets are also available separately)
- 180° rotational head
- Built-in safety valve
- Pressure release lever
- Housed in a moulded plastic carry case
- Comprehensive instructions included

Specifications:

Cable Range:	25-185mm
Crimping Force:	50kN
Rated Operating Pressure:	600 bar (8600 psi)
Connector Type:	Terminal
Maximum Wire Size:	185mm ²
Minimum Wire Size:	10mm ²
Overall Length:	386mm

Professionally approved products.

