

Datasheet

## RS Pro 2.77mm Pitch 9 Way IDC D-sub Connector, Plug, Metal Shell

RS Stock No: **642-4834**



### Product Details

RS Pro 9-way IDC D-sub connector has a low profile metal body construction for added durability. This connector has 9 gold plated contacts for precise connection. This straight D-sub male connector has 2.77 mm pitch.

### Features and Benefits

- Low profile metal body construction
- 9 number of gold plated contact
- 2.77 mm pitch
- Male plug

**Specifications:**

Body Orientation	Straight
Contact Plating	Gold
Gender	Male
Housing Material	Metal
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-55°C
Number of Contacts	9
Pitch	2.77 mm
Insulation Supported	No
Shell Plating	Tin