

## 437 piece PVC Black Grommet Kit



### PVC Black Grommet Kit

A 437 piece black PVC kit containing 8 different sized standard grommets (type 1) and 2 different sized easy fit grommets (type 2). Suitable for use with a panel thickness ranging from 1.7 to 3.4 mm, a panel hole diameter ranging from 6 to 31.7 mm and a cable hole diameter ranging from 3 to 19 mm.

Kit Contents								
Type	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	Qty	Replenishment Stock no.
1	8.5	6.0	3.0	4.7	1.7	n/a	100	<a href="#">666-4593</a>
1	10.2	7.2	5.0	4.4	1.7	n/a	100	<a href="#">666-4596</a>
1	13.3	10.0	6.4	6.3	1.7	n/a	70	<a href="#">666-4590</a>
1	15.5	11.0	7.8	9	3	n/a	35	<a href="#">666-4600</a>
1	19.5	13.9	10.5	6.4	3.4	n/a	40	<a href="#">666-4603</a>
1	23.7	20.1	15.5	6.1	1.7	n/a	25	<a href="#">666-4607</a>

1	29.9	25.1	18.9	7.2	1.5	n/a	15	<a href="#">666-4616</a>
1	38.1	31.7	25.0	7.8	1.5	n/a	12	<a href="#">666-4619</a>
2	23.9	19.6	15.5	2.1	2.0	3.9	25	<a href="#">666-4613</a>
2	30.0	26.0	20.8	2.4	2.4	3.8	15	<a href="#">666-4622</a>

### Expandable cable grommets

These **grommets** are made from extruded neoprene that does not contain latex or wax and does not tarnish silver, with good resistance to ozone, mould formation and aromatic fuels. Insulation resistance  $5 \times 10^{10} \Omega$  (dry) at 20°C. Temperature range: -65°C to +90°C in continual operation. The grommets are fitted using the manual **grommet pliers** that ensure rapid and easy grommet fitting. A **lubricant** can be used to facilitate grommet fitting. This should be used sparingly on the pins of the grommet. Also suitable as lubricant for all rubber and PVC products. The grommets comply with the specifications of B.S. 3858.