

Datasheet

## RS Pro IP44 Purple Surface Mount 3P Right Angle Industrial Power Socket, Rated At 16A, 20 to 25 V

RS Stock No: **668-5373**



### Product Details

RS Pro IP44 purple surface mount 3P right angle industrial power socket has a voltage rating of 20 to 25 V, current rating of 16 A and temperature rating of -25 to +40°C. It features robust design with plastic construction for durability. This splash proof, female power socket is well suited to industrial purposes.

### Features and Benefits

- Low voltage surface socket
- This splash proof, female socket is well suited to industrial purposes
- Made from engineering plastic
- Screw down termination method

**Specifications:**

|                               |                              |
|-------------------------------|------------------------------|
| Body Orientation              | Right Angle                  |
| Colour                        | Violet                       |
| Current Rating                | 16 A                         |
| Gender                        | Female                       |
| IP Rating                     | IP44                         |
| Low Voltage                   | Yes                          |
| Maximum Operating Temperature | +40°C                        |
| Minimum Operating Temperature | -25°C                        |
| Mounting Type                 | Surface Mount                |
| Plug/Socket                   | Socket                       |
| Pole Format                   | 3P                           |
| Termination Method            | Screw Down                   |
| Voltage Rating                | 20 to 25 V                   |
| Operating Frequency           | 50/60 Hz                     |
| Outlet Port                   | M20 x 1.5                    |
| Standards Met                 | IMQ - ENEC 03, EN 60309-1, 2 |