

Datasheet

RS Pro IP44 Purple Surface Mount 2P Right Angle Industrial Power Socket, Rated At 16A, 20 to 25 V

RS Stock No: **668-5379**



Product Details

RS Pro IP44 purple surface mount 2P right angle industrial power socket has a voltage rating of 20 to 25 V, current rating of 16 A and temperature rating of -25 to +40°C. It features robust design with plastic construction for durability. This splash proof, female power socket is well suited to industrial purposes.

Features and Benefits

- Low voltage surface socket
- This splash proof, female socket is well suited to industrial purposes
- Made from engineering plastic
- Screw down termination method

Specifications:

Body Orientation	Right Angle
Colour	Violet
Current Rating	16 A
Gender	Female
IP Rating	IP44
Low Voltage	Yes
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	-25°C
Mounting Type	Surface Mount
Plug/Socket	Socket
Pole Format	2P
Termination Method	Screw Down
Voltage Rating	20 to 25 V
Operating Frequency	50/60 Hz
Outlet Port	M20 x 1.5
Standards Met	EN 60309-1, 2