

Product Data Sheet

RS Part number	6803858
Part Number	EVA200R20/60BLACK
<u>Overview</u>	200mm Puncture Proof wheel
Manufacturer	Keystone
<u>Attributes</u>	
Load capacity	100kg
Type	Wheel only
Wheel diameter	200mm
Wheel Centre	Polypropylene
Tyre material	Puncture proof rubber
Bore size/type	20mm roller bearing
Tread Width	50mm
Hub Length	60mm

- l) Do not require reinflating when they have stood like a pneumatic tyre does
- l) No costly downtime, service or repairs
- l) Totally puncture proof
- l) Tyre life time up to 4 times that of a pneumatic equivalent
- l) Closed cell construction means it wont absorb water, freeze and then crack like some cheaper versions
- l) Shore hardness gives a shock absorbance and "ride" just like a pneumatic