



LED/Multiled	<i>LED</i>	Optimum voltage (V)	2VDC	Intensity	<i>5mcd@10mA typ</i>
Mounting Size	<i>6MM</i>	Rectifier	-	Reverse Voltage	
Mounting Finish	<i>FLUSH</i>	AC current	-		
Protection	<i>IP67</i>	DC current			
Mount Holder	<i>BLACK Bezel</i>	Voltage Tolerance(%)	10%		
Chip Qty	<i>1</i>	Optimum temperature (°C)	-25°C...+60°C		
Indicator colour	<i>RED</i>	Storage temperature (°C)	-25°C...+60°C		
Wavelength (nm)	<i>625</i>	Contact Tab x 2	<i>Red/Black</i> <i>Insulating wires</i>		



*Dimension in mm (typical), not to scale.
We reserve the right to make changes without further notice to this product to improve reliability, function or design.*