

Antistatic swivel braked castor,80mm



Specifications

Fixing Hole Centres	50 x 36mm
Fixing Hole Size	6.5mm
Hub Bearing Type	Plain Bore
Load Capacity	50kg
Mounting	Plate
Overall Height mm	109
Plate Size	65 x 50mm
Type	Swivel, Braked
Tyre Material	Rubber
Wheel Diameter	80mm
Wheel Material	Anti-static rubber
Wheel Width	20mm