

## Antistatic swivel braked castor, 100mm



### Specifications

Fixing Hole Centres	50 x 36mm
Fixing Hole Size	6.5mm
Hub Bearing Type	Plain Bore
Load Capacity	60kg
Mounting	Plate
Overall Height mm	129
Plate Size	65 x 50mm
Type	Swivel, Braked
Tyre Material	Rubber
Wheel Diameter	100mm
Wheel Material	Anti-static rubber
Wheel Width	30mm