

Professionally approved products.

Datasheet

8 Ohm, 0.15W, 31.9mm Miniature Speaker, 6mm Lead Length

RS Stock number [724-3119](#)



Specification:

- Impedance $8 \pm 15\% \Omega$
- Nominal power 0.15W
- Maximum power 0.20W
- Resonant frequency $1500 \pm 20\% \text{Hz}$
- Frequency range F 500-20,000Hz
- Sound output level at 0.1W/0.5M $84 \pm 3 \text{dB}$
- Operating temperature $-20^\circ\text{C} \sim +60^\circ\text{C}$
- Storage temperature $-30^\circ\text{C} \sim +70^\circ\text{C}$
- Weight $10\text{g} \pm 5\%$

Features:

- ROHS compliant
- Cone material: Mylar
- Pin pitch: 17.5mm
- Housing material: ABS777

All data at 25°C unless otherwise specified

Professionally approved products.

Dimensions:

