## Data sheet RS Essentials

## Electromechanical Buzzer PCB

## Features:

• Colour: Black

• Housing material: Noryl

Sealed base

• Wave solderable and washable

Internal drive circuit

All data at 25°C unless otherwise specified.

SPECIFICATIONS	Electro Mechanical Indicator
Operating Voltage	4-8VDC
Rated voltage	6VDC
Rated Current at rated voltage Max	25mA
Sound Output at 20cm, at rated voltage	≥85dB
Resonant Frequency	2300±500Hz
Tone	Continuous
Operating Temperature	-20 ~ +70°C
Storage Temperature	-30 ~ +80°C
Weight	<b>7</b> g

Dimensions: (Unit: mm; Tolerance: ±0.5m)



