

# Data sheet

## RS Essentials

### 12VDC Electromechanical Buzzer with leads

#### Features:

- Colour: Black
- Housing Material: ABS
- Internal drive circuit

All data at 25°C unless otherwise specified.

| SPECIFICATIONS                         | Electro Mechanical Indicator |
|--|------------------------------|
| Operating Voltage                      | 9 – 15 VDC                   |
| Rated voltage                          | 12 VDC                       |
| Rated Current at rated voltage Max     | 25mA @ 12v                   |
| Sound Output at 20cm, at rated voltage | ≥75dB @ 6v                   |
| Resonant Frequency                     | 400±100Hz                    |
| Tone                                   | Continuous                   |
| Operating Temperature                  | -10 ~ +60°C                  |
| Storage Temperature                    | -10 ~ +70°C                  |
| Weight                                 | 10g                          |

Dimensions: (Unit: mm; Tolerance: ±0.5m)

