

Coloured Stainless Steel Cable Ties



Product Details

Grade 316 stainless steel cable ties with a closed roller ball head, that are available in a range of colours and sizes.

- Polyester coated stainless steel
- Available in a range of colours
- High tensile strength
- Self-locking design
- Tighten by hand or with a tool
- Excellent resistance to high temperature, chemicals, weather and abrasion
- Operating Temp: -80°C to +150°C (coated) -80 °C to +538 °C (uncoated)

Material: Stainless Steel (316 grade)

Application: Maintenance

Dimensions

RS Stock No.	Colour	Length (mm)	Width (mm)	Max bundle Dia. (mm)
743-6212	Red	100	4.6	25
743-6260	Green	100	4.6	25
743-6285	Blue	100	4.6	25
743-6302	White	100	4.6	25
743-6239	Yellow	100	4.6	25
743-6217	Red	125	4.6	25
743-6311	White	125	4.6	25
743-6289	Blue	125	4.6	25
743-6248	Yellow	125	4.6	25



ENGLISH

Coloured Stainless Steel Cable Ties

RS Stock No.	Colour	Length (mm)	Width (mm)	Max bundle Dia. (mm)
743-6226	Red	150	4.6	35
743-6314	White	150	4.6	35
743-6298	Blue	150	4.6	35
743-6267	Green	150	4.6	35
743-6241	Yellow	150	4.6	35
743-6318	White	200	4.6	50
743-6291	Blue	200	4.6	50
743-6276	Green	200	4.6	50
743-6245	Yellow	200	4.6	50
743-6229	Red	200	4.6	50
743-6327	White	200	7.9	50
743-6254	Yellow	200	7.9	50
743-6223	Red	200	7.9	50
743-6279	Green	200	7.9	50
743-6295	Blue	200	7.9	50
743-6320	White	360	4.6	100
743-6305	Blue	360	4.6	100
743-6273	Green	360	4.6	100
743-6232	Red	360	4.6	100
743-6257	Yellow	360	4.6	100
743-6282	Green	360	7.9	100
743-6324	White	360	7.9	100
743-6308	Blue	360	7.9	100
743-6235	Red	360	7.9	100
743-6251	Yellow	360	7.9	100