



30W LED Task Light



Description

This 30W LED task light is supplied with a 5m lead, and is ideal for use on site due to its durable die cast body. This task light is also cool to run and eliminates fire and burn hazards associated with halogen site lighting.

Features

- Daylight (6000K)
- 2100 lumens – replaces a 500W halogen
- Wide beam angle of 150°
- Complete with heavy duty steel floor stand
- 5m lead complete with 16A BS EN 60309 plug
- Cool running – no risk of fire
- IP65
- 110V
- Tripod stand available

Technical Specification

| | |
|----------------|-----------------------|
| Voltage | 110V |
| Lamp Type | COB LED |
| Wattage | 30W |
| Light Output | 2100lm |
| Lamp Col. Temp | 6000K |
| IP Rating | IP65 |
| Body Material | Die Cast Aluminium |
| Frame Material | Steel |

Range

| | |
|--------------------|---------|
| 30W LED Task Light | 7884616 |
| Tripod Stand – 2m | 7884625 |

Dimensions (mm)

| | Height | Width | Depth |
|---------|--------|-------|-------|
| 7884616 | 310 | 295 | 190 |

Standards

- BS EN 5098-1: 2008+A11: 2009
- BS EN 60598-2-5: 1999
- BS EN 61347-1: 2008
- BS EN 61347-2-13: 2006
- BS EN 55015: 2006+A2: 2009
- BS EN 61547: 2009
- BS EN 61000-3-2: 2006+A2: 2009
- BS EN 61000-3-3: 2008
- BS EN 60309: 1999