


NO	DESCRIPTION	DATE
①	31.9±0.5 → 31.8±0.5	10.20.99'
②	BACKGROUND FORMAT UPDATED	02.19.05'
③	DEL. Ø4.000 BACKGROUND FORMAT UPDATED	05.10.11'
④	DEL. PROOF VOLTAGE WORKING VOLTAGE 11.4 → 10.8 ; ADD INSULATION 31.8±0.5 → 30.5±0.5 -40° C TO +60° C → -55° C TO +85° C PDM → TEFLON ; ADD VSWR Ø18.0 → Ø16.0 MODIFICATION PARTS ② ⑤	08.17.13'



### 1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-300 MHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 VOLTAGE RATING: 500 VOLTS MAX. ④
- 1.4 VSWR: 1.3 MAX. ④

### 2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3804
- 2.2 CENTER CONTACT: BRASS PER JIS-C3804
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710 ④

### 3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

### 4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +85° C ④

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
6	SHELL	BRASS	1	SILVER 70 μ"MIN.
5	CENTER CONTACT	BRASS	1	GOLD
4	WASHER	BRASS	1	NONE
3	INSULATION II	TEFLON	1	NONE
2	BODY	BRASS	1	SILVER 70 μ"MIN.
1	INSULATION I	TEFLON	1	NONE
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		STRAIGHT UHF PLUG-BNC JACK ADAPTER			
製圖	DRAWN	TOLERANCE	品名	17-19-3	T.G.S
檢圖	CHECK	.X ±0.2	TITLE	\ROHS COMPLIANT (<50Ω)	
認定	APPROVAL	.XX ±0.1	單位	mm(in)	DWG.NO. 17-0081
		.XXX ±0.05	比例	SCALE	7902818
		ANGLE ±5°			

