


NO	DESCRIPTION	DATE
△	MODIFY PARTS ①④ 25.0 → 22.0 33.6±0.5 → 30.5±0.5	08.05.13'



**1.0 ELECTRICAL**

1.1 FREQUENCY RANGE: DC-250 MHz  
1.2 NOMINAL IMPEDANCE: 75 OHMS

**2.0 MATERIALS**

2.1 BODIES: BRASS PER JIS-C3604  
2.2 CENTER CONTACT: BRASS PER JIS-C3604

**3.0 FINISHES AND OTHERS**

3.1 SEE BELOW TABLE FOR DETAILS.

**4.0 ENVIRONMENTAL**

4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
5	INSULATION	POM	1	NONE
4	CENTER CONTACT	BRASS	1	GOLD
3	INSULATION	POM	1	NONE
2	WASHER	BRASS	1	NICKEL
1	BODY	BRASS	1	NICKEL 100μ" MIN.

(P/N:546-2936)

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		STRAIGHT RCA PLUG - BNC JACK ADAPTER	
製圖	DRAWN Yoko	TOLERANCE .X ±0.2	品名 14-05-1 D.G.N
檢圖	CHECK Angela	.XX ±0.1	UNIT mm(in)
認定	APPROVAL Angela	.XXX ±0.05	SCALE 4:1
		單位	DWG.NO. 14-0013
		比例	7902809
		DATE	04.17.93'
		版次	B-1
		REV.	
		ROHS COMPLIANT (750)	

