

Professionally approved products.

Datasheet

SPST Rocker Switch

RS Stock number 793-2541



Specifications:

Rating:	6(2)A 250 VAC T125/55 1E4, 10A 125VAC
Colour:	White Body White Rocker 0/1 Engraving
Switching Action:	Single Pole Momentary
Contact Diameter:	P4 (1.6mm)
Contact Resistance:	30m Ohms Max
Insulation Resistance:	500VDC 100M Ohms Min
Electrical Life:	10,000 cycles
Operation force:	300 – 600gf
Operating Temperature Range:	-25 - 125°C
Housing Material:	Nylon #66 UL 94V-2
Rocker Material:	Nylon #66 UL 94V-2
Terminal Material:	Copper Alloy SN or AG plated
Contact Material:	AgNi (15) alloy

Professionally approved products.
Datasheet
Dimensions - mm

