



Professionally approved products.

Specifications:

1. Power Consumption: 60W
2. Input Voltage: 220VAC±10% 50Hz
3. Output Voltage: 24VAC
4. Temperature range: 150 ~ 450°C Temperature stability: ±2
5. Temperature Accuracy: ±15°C
6. Tip to Ground Impedance: <math><2\Omega</math>
7. Tip to Ground Voltage: <math><2\text{mV}</math>
8. Setting Mode: rotational controller adjustment and immediate access
9. Temperature-correcting Mode: Digital
10. Heating Core: 60W two-core ceramics heating core
11. Physical Dimension of Principal Machine: 167(L)×138(W)×97(H)mm
12. Weight: 1.9KG



Features:

Brand new shape design, HD LCD display and elegant appearance...

Digital temperature calibration

Wide options of soldering tips

Made of conductive materials, anti-statics.