




Datenblatt - Fiche technique - Data sheet


RS Stock Number: 815-8560





ELECTRICAL TEST:

1. 100% OPEN SHORT & MIS WIRE TEST
2. CONTACT RESISTANCE: 2 OHM (MAX.)
3. INSULATION RESISTANCE: 10M OHM (MIN.)
4. HI-POT TEST: DC 300V/10ms



10	W=20MM 25u DOUBLE CONDUCTIVE COPPER FOIL	0.02	m
9	DP M (DP M/HDMI A F PCB) ABS One-piece SHELL WHITE PRINT: ㄣ (PT:COOL GRAY 8C W:5.0MM)	1	pcs
8	DP M (DP M/HDMI A F PCB) ABS WHITE	1	pcs
7	φ 0.8 heat shrinkable TUBE 6mm*5pcs	0.03	m
6	DisplayPort M TRANSPARENT COLOR PVC DUST COVER	1	pcs
5	HDMI A F ABS One-piece SHELL Apple SNOWY WHITE	1	pcs
4	HDMI A F ABS One-piece WHITE PRINT: DP 1.2 (neutral)	1	pcs
3	65P SNOWY WHITE PVC	9	g
2	empty PCB + SMT + PLATED: NICKEL	1	pcs
1	DP M TO M SNOWY WHITE PLATED: NICKEL 34AWG AL 0.4M 5 Pair twist	1/2	pcs
NO	DESCRIPTION	QTY	UNIT

TOLERANCE			DRAWN BY	Item No.:	815-8560
	INCHES	M/M			
.X	.015	.30			
.XX	.010	.10			
.XXX	.005	.05			
CHECK BY	SCALE	NONE	DRAWING NO.:	REV. A	
APPD BY	UNIT	MM			
	DATE	2014.02.27		1/3	