

Micro USB Power Adapter 5Vdc 5W UK Plugtop



Features

- Universal AC Input
- UK Plugtop
- Small & Compact Design
- Micro USB Output
- Over Voltage, Over Current & Short Circuit Protections
- ErP Level V
- RoHS Compliant
- MTBF >50,000 hours

RS Stock Number	Manufacturers P/N	Output Voltage	Output Current (Min)	Output Current (Max)	Power (Watts)	Line Regulation	Voltage Tolerance	Ripple & Noise (mV- p-p)
8280217	T5586ST	+/- 5Vdc	0A	1A	5W	+/-3%	+/-5%	200mV

Input

- Rated Input 100-240Vac
- Rated Input Frequency 50-60Hz
- Input Current 0.2A
- Leakage Current 0.25mA
- UK Plugtop

Output

- 1.5M Lead with Micro USB

Environmental

- Operating Temperature 0°C to 40°C
- Storage Temperature -20°C to 60°C
- Operating Humidity 20% to 85%
- Storage Humidity 5% to 95%

Casing

- Dimensions 67mm x 49.55mm x 64.8mm
- Weight 80g (approx.)

