



| | | | | | |
|----------------------|----------------------|----------------------------|----------------------|-----------------------------|---------------------|
| LED/Multiled : | <i>LED</i> | Optimum voltage (V) : | <i>110VAC</i> | Intensity : | <i>1300mcd@20mA</i> |
| Mounting Size : | <i>8mm</i> | Rectifier : | <i>-</i> | | |
| Bezel Finish : | <i>Bright Chrome</i> | AC current : | <i>6mA-</i> | | |
| Sealing Protection : | <i>IP67</i> | DC current : | | | |
| Bezel Style : | <i>Prominent</i> | Voltage Tolerance(%) : | <i>10%</i> | | |
| Chip Qty : | <i>1</i> | Optimum temperature (°C) : | <i>-40°C...+85°C</i> | Principal Attributes | |
| LED colour : | <i>Yellow</i> | Storage temperature (°C) : | <i>-40°C...+85°C</i> | | |
| Wavelength (nm) : | <i>589</i> | Contact Tab x 2 : | <i>2.8x0.8mm</i> | | |



*Dimension in mm (typical), not to scale.
We reserve the right to make changes without further notice to this product to improve reliability, function or design.*