



LED/Multiled :	LED	Optimum voltage (V) :	220VAC	Intensity :	50mcd@20mA
Mounting Size :	8mm	Rectifier :	-		
Bezel Finish :	Bright Chrome	AC current :	3mA		
Sealing Protection :	IP67	DC current :			
Bezel Style :	Flush	Voltage Tolerance(%) :	10%		
Chip Qty :	1	Optimum temperature (°C) :	-40°C...+85°C	Principal Attributes	
LED colour :	Blue	Storage temperature (°C) :	-40°C...+85°C		
Wavelength (nm) :	470	Contact Tab x 2 :	2.8x0.8mm		



Dimension in mm (typical), not to scale.
 We reserve the right to make changes without further notice to this product to improve reliability, function or design.