

Datasheet

RS Pro 910 Series 5.08mm Pitch Straight PCB Terminal Block with Plug In Termination, Screw, 3 WayRS Stock No: **874-4818****Specifications:**

Body Orientation	Straight
Colour	Green
Current Rating	15 A (UL), 20 A (IEC)
Depth	15.1 mm
Gender	Female
Length	25.4 mm
Material	Nylon 66
Mounting Type	Screw
Number of Contacts	3
Number of Rows	1
Pitch	5.08 mm
Termination Method	Plug In
Type	Plug
Voltage Rating	300 V (UL), 320 V (IEC)
Width	18 mm



ENGLISH

American Wire Gauge	14 to 28 AWG
Insulation Withstands Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ
Flammability Rating	UL 94 V-0