

739-8449 Data Sheet

ENGLISH

RS stock number : 739-8449

Type of tool : Mini 1/4" Ratchet

Power Source : Compressed air Maximum permissible operating pressure : 90 psi (6.2 bar) : 90 psi (6.2 bar)

Features

Palm size Ratchet allows the operator to reach small areas Compact and lightweight design allows maximum operator control and performance

Rear exhaust to keep airflow away from work area High power motor for consistent performance

Specifications

Anvil Size: 1/4"

Max Torque: 34Nm / 25ft-lb Free Speed: 300RPM Weight: 0.49kgs Length: 5.08" / 128mm

Min Hose Size: 3/8" / 10mm Air inlet thread: 1/4

Sound: 80dBA Vibration: 3.78m/s²

Ave Air Consumption: 1.8cfm /50 l/min

Recommended lubrications: 10 Weight SAE Oil

739-8449

Mini 1/4" Ratchet

Technical Data



Declaration of Conformity

We RS Components Ltd

declare under our sole responsibility that the

739-8449 - Mini 1/4" Ratchet

conforms with the directive

and the standards

2006/42/EEC EN 792-6 ISO 28927

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.