

Eaton FI-25/4/003-A

Catalog Number: FI-25/4/003-A

Eaton residual current circuit breaker, Type A FI Residual-current circuit breaker, DC and pulsed current sensitivity, top-hat rail mounting, 25 A, Four-pole, 230/400 V, Twin-purpose, 30, MilliAmpere



General specifications

Product Name	Catalog Number
Eaton residual current circuit breaker	FI-25/4/003-A
EAN	Product Length/Depth
4015082792138	3 in
Product Height	Product Width
3 in	3 in
Product Weight	Certifications
1 lb	EN 61008 IEC 61008

Physical Attributes

Mounting Method

Top-hat rail

Number of poles

Four-pole

Terminals

Twin-purpose

Type

Type A

Performance Ratings

Amperage Rating

25 A

Fault current

0.03 mA

Resources

Specifications and datasheets

[Eaton Specification Sheet - FI-25/4/003-A](#)

[Product Data Sheet - FI-25/4/003-A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)