

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

SHC1021CR -- Cord Connectors



Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue.

Product Specifications

Product Type	Cord Connectors
Material/Style	Nylon Standard Style
Cord Diameter Range	.19"-.25" (4.7- 6.3)
Cord Connector Body Style	Straight Male
Form Size	F2
HUB Size	1/2"
Color Code	Red
Effective Operating Temperature	-30°F to +225°F (-34°C to +107°C)
Recommended Knockout Hole Size	.86"-.91" (21.8-23.0)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	1.32" (33.5) Dia.
Dimension B	1.50" (38.1) Ref.
Dimension C	.53" (13.5)
Dimension D	.58" (14.7) Throat Dia.
Dimension E A/C	1.25" (31.7)
Dimension E A/F	1.12" (28.4)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UPC Number	78358520803
Weight in LBs	0.15
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

