

TURCK M8 picofast® Connectivity

M8 picofast® to M12 eurofast® Adapters

- Enables *picofast* and *eurofast* Connectors to be Interchanged
- *eurofast* Connection has Anti-vibration Coupling Nut
- IEC IP67 Protection



Housing Style	Part Number	Features	Wiring Diagram
<p>FKMR 4 ..</p>	FKMR 4-ESM 3S	TPU body, 60 VAC/ 75 VDC, 4 A, 80°C, female eurofast, male snap-lock picofast connector, 3-pin	
	FKMR 4.4-ESM 4S	TPU body, 30 VAC/ 36 VDC, 4 A, 80°C, female eurofast, male snap-lock picofast connector, 4-pin	
<p>FSMR 4 ..</p>	FSMR 4-SKM 3	TPU body, 60 VAC/ 75 VDC, 4 A, 80°C, male eurofast, female threaded picofast connector, 3-pin	
	FSMR 4.4-SKM 4	TPU body, 30 VAC/ 36 VDC, 4 A, 80°C, male eurofast, female threaded picofast connector, 4-pin	

Add "/S857" to the end of part description to specify addition of mounting hole.

Pinouts

Female			Male		
3-Pin picofast	4-Pin picofast	4-Pin eurofast	3-Pin picofast	4-Pin picofast	4-Pin eurofast