

558-00063

Article Number: 558-00063

SwiftMark Self-Laminating Label, .8" X .35" X .94", Vinyl, White, 2500/RL



Download drawing



Download spec sheet

Base Data

Local Order Number 558-00063

Type TAG20-47W203SM

Color White (WH)

- Features and Benefits**
- HellermannTyton SwiftMark Self-Laminating Labels come on rolls for convenient loading and printing.
 - Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time.
 - Labels are UL recognized for indoor and outdoor use to expand application options.
 - HellermannTyton SwiftMark Self-Laminating labels are designed for high speed printing and dispensing to work flawlessly in the SwiftMark applicator and printer.

Color Marking Field White (WH)

Product Description HellermannTyton's self-laminating labels are designed for use in the SwiftMark automatic label applicator and printer. Manufactured in a conformable frosty clear vinyl with good contrast clarity, they are designed with a clear overlap to protect the printed text. The labels come 1 across on a spindle that fits into the applicator. Labels are designed with a special adhesive that bonds quickly to wire and cable using a custom high speed dispensing liner. The printed labels can be used on wires as small as .06" (1.52mm) in diameter and as large as .75" (19mm) in diameter. A UL recognized mark for indoor and outdoor use can be achieved using the TT100 series ribbon (part no. 556-00165). SwiftMark vinyl label meet all the requirements of UL969 - STANDARD FOR MARKING AND LABELING SYSTEMS edition -4. Labels UL recognized under UL file number MH18396. The SwiftMark can accept labels widths that range from .5" (12.7mm) to 2.0" (50.8mm).

Mounting method Identification ETIM Pasting / Stick

Short Description SwiftMark Self-Laminating Label, .8" X .35" X .94", Vinyl, White, 2500/RL

Product Dimensions

Variant Roller form

Width W (Imperial) 0.8 "

Width W (Metric) 20.3 mm

Height H (Imperial) 0.35 "

Height H (Metric) 8.89 mm

Height H2 (Imperial) 0.94 "

Height H2 (Metric) 23.87 mm

Bundle Diameter Min. (Imperial) 0.078 "

Bundle Diameter Min. (Metric) 2.0 mm

Bundle Diameter Max. (Imperial) 0.18 "

Bundle Diameter Max. (Metric) 4.7 mm

Outside Diameter Min. (Imperial) 0.078 "

Outside Diameter Min. (Metric) 2.0 mm

Outside Diameter Max. (Imperial) 0.18 "

Outside Diameter Max. (Metric)	4.7 mm
Horizontal Repeat HR (metric)	20.3 mm
Horizontal Repeat HR (imperial)	.8 "
Print Method	Thermal Transfer
Thickness T (Metric)	25 µm
Vertical Repeat VR (imperial)	1.31 "
Vertical Repeat VR (metric)	33.27 mm
Width of Liner WL (imperial)	1.125 "
Width of Liner WL (metric)	31.75 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	2500
Package Quantity (Metric)	2500
Carton Quantity	2500
Labels per Row	1
Weight (imperial)	1.27 lbs
Weight (Metric)	0.58 kg

Material and Specifications

Material	Type 100, Vinyl (PVC), white (WH), self laminating
Material Shortcut	100B
Adhesive Shortcut	Acrylic
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Operating Temperature	-51°F to +200°F (-46°C to +93°C)
ROHS Compliant	Yes
Certification/Specification	UL-Recognized