



Representative

Catalog Number: E977EC
Product ID: 7TAA232220R0011
UPC Number: 03448106942
EAN Number: 05415022420326
Status: Active

Conduit Clamp, Size 3/4 Inch, Length 2.40 Inches, Width 0.50 Inches, Height 1.255 Inches, Material PVC, Color Gray

- Non-metallic clamps offer the same chemical resistance as Carlon non-metallic conduits for a complete, corrosion resistant system.

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Carlon
Type	Conduit Clamps & Support Straps
Special Features	Non-metallic clamps offer the same chemical resistance as Carlon non-metallic conduits for a complete, corrosion resistant system.
Application	UV inhibited for use in direct sunlight.
Size	3/4
Material	Non-Metallic

European Specifications (ETIM)

ETIM	EC000127 Saddle
Model	Closed
Type of fastening	Screw hole
Material	Plastic
Plastic sheathed	Y

Packaging

Outer Quantity	100
Outer Dimensions (inches)	7.9x6.5x5.7
Weight Uom	0.02 lbs. Each

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-ac03405

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com