

PLUG-IN RELAY COMPLETE UNIT AC 24V, 4 CO CONTACT LED MODULE RED STANDARD PLUG-IN SOCKET SCREW TERMINAL 3.5 MM PINNING



Figure similar

General technical data:		
Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
Type of voltage		AC
Control supply voltage		
• at AC		
— at 50 Hz Rated value		
— minimum	V	24
— maximum	V	24
— at 60 Hz Rated value		
— minimum	V	24
— maximum	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		4
Operating current of the auxiliary contacts		
• at DC-13		

- at 24 V
- at AC-15
- at 230 V

A	4
A	4
Design of the switching function positively driven	No
Switching behavior	monostable

Mechanical data:

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	28
Height	mm	72
Depth	mm	74

Certificates/ approvals:

General Product Approval

Declaration of Conformity



Further information

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT5A5R24>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT5A5R24>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT5A5R24&lang=en

last modified:

18.07.2015