

Solid Copper Alligator Clip, 10 Amp

Features

- Crimp/Solder Connection
- Overall Length: 1.690" (42.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-160	Solid Copper Alligator Clip

See page 26 for recommended insulators.



See page 18 for clip & insulator combinations.

Phone Tip Steel Alligator Clip, 10 Amp

Features

- Nickel Plated Clip
- Accepts Standard Phone Tip or Test Probe Tip
- Overall Length: 1.970" (50mm)
- Jaw Opening: .310" (7.9mm)

NTE Type No.	Description
72-181	Phone Tip Steel Alligator Clip

See page 25 for recommended insulators.



Solid Copper Alligator Clip w/Screw, 10 Amp

Features

- 6-40 Screw or Crimp Connection
- Overall Length: 1.690" (42.86mm)
- Jaw Opening: .310" (7.9mm)

NTE Type No.	Description
72-187	Solid Copper Alligator Clip with Screw



Steel Alligator Clip, Fang Tooth w/Barrel

Features

- Nickel Plated Clip
- Crimp/Solder or Banana Plug Connection
- Grips Both Fine and Thick Conductors
- Overall Length: 1.920" (48.7mm)
- Jaw Opening: .390" (9.9mm)

NTE Type No.	Description
72-098	Steel Alligator Clip, Fang Tooth with Barrel

