

FT-100 Level Float Switch



Flexible by Design

The FT-100 Level Float Switch is a single point level sensor that switches ON or OFF at one level. They work well as alarm point indicators. The switch operating levels are easily adjustable and designed for use in water and sewage applications.

Features

- Highly chemical resistant
- Proven reliability in operation
- Not sensitive to rotation

FT-100 Specifications



Performance

- Switching Differential:
1.5 in. above or below horizontal
- Maximum Pressure: 13 psi (0.9 bar)
- Maximum Water Depth: 30 ft (9m)

Electrical

- Voltage: 125/250 VAC
- AC Current (Resistive): 5 A
- 50/60 Hz

Connectivity

- Cable: 18 gauge, 2 conductor

Physical

- Standard Cable Lengths:
6m (20 ft)
9m (30 ft)
- Weight: 1 lb

Environmental

- Max. Liquid Temperature:
140°F (60°C)

Certification

- CSA General Purpose
- UL
- CPE (water resistant)

