

EAO – Your Expert Partner for Human Machine Interfaces

45-290J.4F00.111 - Keylock switch 2 positions

45-290J.4F00.111 - Keylock switch 2 positions



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out \varnothing 30.5 mm

Front

Front ring material Metal mat
Front ring colour sandgrey
Front shape round
Front dimension \varnothing 38 mm

Other Attributes

Weight 0.090 kg

Operating-/Indication part

Switching angle $C = 90^\circ$

IP-Rating

Front protection IP66, IP67, IP69K

Actuator

Key remove A
Switching action Rest - Maintained
Housing material Metal

Switching element

Rotary positions 2
6

Function

Keylock switch

EAO – Your Expert Partner for Human Machine Interfaces

45-290J.4F00.111 - Keylock switch 2 positions

Wiring diagram



Switching positions

A C



Additional information

The standard lock: RONIS, T254
Front panel thickness 1-6 mm max.

Legend

Switching action: A = Rest, B = Momentary