



SPECIFICATIONS						
HOUSING MATERIAL/COLOR	NYLON/BLACK					
CONTACT MATERIAL/PLATING	BRASS/GOLD					
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL					
RATED CURRENT [A]	4.0 A					
RATED VOLTAGE [V]	30 VAC/36 VDC					
MAXIMUM WIRE SIZE	18 AWG					
CABLE GRIP RANGE	6-8mm					
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)					
PROTECTION CLASS	IEC IP67					



RWC 09/29/08 22596

ECO NO.

DATE



B UPDATE CONTACT MATERIAL/PLATING, ECO

REV DESCRIPTION

## SOURCE DRAWING - FOR REFERENCE ONLY

	RELATED DOCUMENTS  1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 High Technology Sensors and Automation Controls (763) 553-7300 (763) 553-0708 fast turck.com			
	MATERIAL		DRFT	RDS	DATE 07/19/07	DESCRIPTION BS 8251-0/PG9/DN		
	SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	DSGN		SCALE 1=1.0	BS 8251-0/	PG9/DNET	
		DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMEN	ASUREMENT			
١	FINISH	NEI ERENCE ONEI				IDENTIFICATION NO.		REV
	SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	MILLIMETERS		ETERS	U3-01272		В
			I 6	O NOT SCALE	THIS DRAWING	FILE: 113-01272	SHEET	1 OF 1