



MALE END VIEW



SPECIFICATIONS

HOUSING MATERIAL/COLOR	POLYAMIDE/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/FINISH	ALUMINUM/BLACK-ANODIZED
O-RING MATERIAL	BUNA-N
RATED CURRENT [A]	UP to 15.0 A
RATED VOLTAGE [V]	600 V
WIRE SIZE RATING [AWG]	14-22 AWG
CABLE DIAMETER RANGE	5-13mm
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	IP67



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1. 2. 3. 4.				DRFT RDS	DATE 11/23/10	DESCRIPTION	
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DSGN	SCALE 1=1.0	BY 4140-0 5-13MM	
SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT		IDENTIFICATION NO.	
FINISH		MILLIMETER [INCH]		DO NOT SCALE THIS DRAWING		REV	
SEE SPECIFICATIONS						U2-18363	
A DRAWING RELEASE		RDS 11/24/10		FILE: U2-18363		SHEET 1 OF 1	
REV	DESCRIPTION	BY	DATE	ECO NO.			