



**Description**

6V 20W T2-1/2 G4 Bi-pin Base

Specifications	
<b>Bulb Type</b>	T-2 1/2
<b>Base Type</b>	G4 (Sub-Miniature 2-Pin)
<b>Filament</b>	C-6
<b>Special Desc</b>	Halogen
<b>MOL in/mm</b>	1.1/28
<b>MOD in/mm</b>	0.35/9
<b>LCL in/mm</b>	0.77/19.5
<b>Volts</b>	6
<b>Watts</b>	20
<b>Lumens</b>	570
<b>CT deg K</b>	3000
<b>Avg Life</b>	2,000
<b>Type Use</b>	Acuity (Eye Chart) Projection
<b>Photo No</b>	343
<b>ANSI Code</b>	ESB/FHE

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335