

150P25/10



Description

120V 150W P25 Medium Base C7A Filament Spot Light

Specifications

Bulb Type	P-25
Base Type	Medium Screw (E26)
Filament	C-7A
Special Desc	Spot, with Vibration-Resistant filament
MOL in/mm	4.75/120.7
MOD in/mm	3.13/79.4
Volts	120
Watts	150
Watts Amps	150
Amps	1.25
Lumens	2100
Avg Life	200
Photo No	500
Coating	Inside Frost

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335