



Description

130V 15W T-6 Candelabra Base

Specifications

Bulb Type	T-6
Base Type	Candelabra Screw (E12)
Filament	C-7A
Special Desc	
MOL in/mm	3.06/77.7
MOD in/mm	0.77/19.6
Volts	130
Watts	15
Amps	0.12
Lumens	90
Avg Life	2,000
Photo No	92
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335