



Description

120V 250W T10 E-26 Base AX2-Q Filament Halogen Frosted

Specifications

Bulb Type	T-10
Base Type	Medium Screw (E26)
Filament	CC-8
Special Desc	Halogen
MOL in/mm	4.0/101
MOD in/mm	1.25/31.8
LCL in/mm	2.25/57.2
Volts	120
Watts	250
Lumens	4600
CT deg K	2900
Avg Life	1,500
Photo No	557
Burning Position	Universal
Coating	Frosted

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335