



Description

130V 25W T-10 Medium Base

Specifications

Bulb Type	T-10
Base Type	Medium Screw (E26)
Filament	C-5V
Special Desc	
MOL in/mm	5.19/131.8
MOD in/mm	1.25/31.8
Volts	130
Watts	25
Amps	0.19
Lumens	180
Avg Life	2,000
Photo No	47
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335