

# 25T6-1/2DC-130V



**Description**

130V 25W T6-1/2 DC Bayonet Base

Specifications	
<b>Bulb Type</b>	T-6 1/2
<b>Base Type</b>	DC Bayonet (BA15d)
<b>Filament</b>	C-8
<b>Special Desc</b>	
<b>MOL in/mm</b>	5.5/139.7
<b>MOD in/mm</b>	0.83/21.1
<b>Volts</b>	130
<b>Watts</b>	25
<b>Amps</b>	0.19
<b>Lumens</b>	210
<b>Avg Life</b>	3,000
<b>Photo No</b>	96
<b>Coating</b>	Clear

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335